

Product data sheet

Specifications

Linergy FT, Comb busbar, 63A, 2 tap-offs, 45mm pitch



GV2G245

Main

Range	Linergy
Product name	FT
Device short name	GV2G
Product or component type	Comb busbar
Accessory / separate part category	Connection accessory
Poles description	3P
Range compatibility	TeSys GV2 TeSys Deca TeSys U
Number of tap-offs	2
[I _{th}] conventional free air thermal current	63 A
Connection pitch	45 mm

Complementary

Fixing mode	Terminals:
[U _i] rated insulation voltage	690 V
Length	89 mm
Product weight	0.036 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2 cm
Package 1 Width	4 cm
Package 1 Length	9.5 cm
Package 1 Weight	37 g
Unit Type of Package 2	S01
Number of Units in Package 2	100
Package 2 Height	15 cm
Package 2 Width	15 cm
Package 2 Length	40 cm
Package 2 Weight	3.862 kg

Unit Type of Package 3	P06
Number of Units in Package 3	3200
Package 3 Height	77 cm
Package 3 Width	80 cm
Package 3 Length	60 cm
Package 3 Weight	130.9 kg

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Environmental Disclosure

[Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard **Yes**

Packaging without single use plastic **No**

[EU RoHS Directive](#) **Compliant**

Use Again

Repack and remanufacture


End of life manual availability [End of Life Information](#)

Take-back **No**


WEEE Label The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Dimensions Drawings

Sets of Busbars GV2G... with Terminal Block GV1G09



Sets of Busbars GV2G245, GV2G254, GV2GR272



	I
GV2G245 (2 x 45 mm)	89
GV2G254 (2 x 54 mm)	98
GV2G272 (2 x 72 mm)	116