

Product data sheet

Specifications



Battery charger, Harmony eXLhoist, compact, multicharger power supply, 6W, 5V DC, 1.2A

ZARC701

Main

Range of product	Harmony eXLhoist
Accessory / separate part type	Battery charger
Product or component type	Battery charger
Accessory / separate part category	Electrical accessory

Complementary

[Us] rated supply voltage	100...240 V AC
Network frequency	50...60 Hz
Nominal output current	1.2 A at 5 V DC
Connections - terminals	5-position plug-in connector
Product weight	0.1 kg

Environment

Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-20...60 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6 cm
Package 1 Width	9.4 cm
Package 1 Length	15.2 cm
Package 1 Weight	196 g
Unit Type of Package 2	S03
Number of Units in Package 2	18
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	3.957 kg



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	6e438e59-42d1-4633-bfe2-cb5ef607659b
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

 Repack and remanufacture	
Take-back	No