

Product data sheet

Specifications



Mounting plate, Linergy HK, 1P+N,
25A, 4.4mm², 105x54x61mm

AK5PA211N3

Main

Range	Linergy
Product name	HK
Product or component type	Mounting plate
Poles description	1P + N
[Ith] conventional free air thermal current	25 A
I ² t on activation	200000 A².s
Number of cables	2 cable(s) 4 mm² at 105 °C
Width	54 mm
Height	105 mm
Depth	61 mm

Complementary

[Ui] rated insulation voltage	690 V conforming to IEC 60439-1
9 mm pitches	6
Product weight	0.135 kg

Environment

Standards	IEC 60439
Product certifications	LROS (Lloyds register of shipping) UL CSA DNV

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.3 cm
Package 1 Width	7.3 cm
Package 1 Length	12.0 cm
Package 1 Weight	208.0 g

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant

Use Again

 Repack and remanufacture	
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins