

# Product data sheet

Specifications



## Mounting plate, Linergy HK, 2P, 25A, 4.4mm<sup>2</sup>, 105x54x61mm

AK5PA211PH13

### Main

Range	Linergy
Product name	HK
Product or component type	Mounting plate
Poles description	2P
[I <sub>th</sub> ] conventional free air thermal current	25 A
I <sup>2</sup> t on activation	200000 A <sup>2</sup> .s
Number of cables	2 cable(s) 4 mm <sup>2</sup> at 105 °C
Width	54 mm
Height	105 mm
Depth	61 mm

### Complementary

[U <sub>i</sub> ] rated insulation voltage	690 V conforming to IEC 60439-1
9 mm pitches	6
Product weight	0.135 kg

### Environment

Standards	IEC 60439
Product certifications	UL CSA LRROS (Lloyds register of shipping) DNV

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.3 cm
Package 1 Width	7.3 cm
Package 1 Length	12.0 cm
Package 1 Weight	235.0 g

### Contractual warranty

Warranty	18 months
----------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
<a href="#">EU RoHS Directive</a>	Compliant

## Use Again

### Repack and remanufacture

Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins