

Product data sheet

Specifications



Selector switch, Harmony XAC,
plastic, black, 2 positions, left
withdrawal position, stay put

ZA2BG2

Product availability: Non-Stock - Not normally stocked in
distribution facility

Main

Range of Product	Harmony XAC
Product or Component Type	Selector switch
Component name	ZA2
Product Compatibility	XACA

Complementary

Net Weight	0.093 lb(US) (0.042 kg)
Cap/operator or lens colour	Black
Marking	Unmarked
Mounting Location	Front of enclosure Base of enclosure
Sale per indivisible quantity	1

Environment

Standards	IEC 60947-5-1 CSA C22.2 No 14 UL 508 IEC 60204-32
Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Vibration resistance	15 gn (f= 10...500 Hz) conforming to IEC 60068-2-6
Shock resistance	100 gn IEC 60068-2-27
Overvoltage category	Class II conforming to IEC 61140
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK08 conforming to IEC 62262

Ordering and shipping details

Category	US10CS222460
Discount Schedule	0CS2
GTIN	3389110648621
Returnability	Yes
Country of origin	FR

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	1.50 in (3.8 cm)
Package 1 Width	2.83 in (7.2 cm)
Package 1 Length	3.86 in (9.8 cm)
Package weight(Lbs)	1.8 oz (50.0 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	2.36 in (6.0 cm)
Package 2 Width	6.69 in (17.0 cm)
Package 2 Length	11.02 in (28.0 cm)
Package 2 Weight	17.9 oz (508.0 g)
Unit Type of Package 3	S02
Number of Units in Package 3	50
Package 3 Height	5.91 in (15.0 cm)
Package 3 Width	11.81 in (30.0 cm)
Package 3 Length	15.75 in (40.0 cm)
Package 3 Weight	6.314 lb(US) (2.864 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	1
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No