

Product data sheet

Specifications



PanelSeT CRN plain door w/o
mount.plate. H600xW500xD200
IP66 IK10 RAL7035..

NSYCRN65200

Product availability: Stock - Normally stocked in distribution facility

Main

Range	PanelSeT
Product name	PanelSeT CRN
Application	Multi-purpose
Category	Compact enclosure
Enclosure nominal height	23.6 in (600 mm)
Enclosure nominal width	19.7 in (500 mm)
Enclosure nominal depth	7.9 in (200 mm)
Installation accessory type	Wall-mounting
Device composition	1 body 1 cable gland plate 1 door 1 lock
Door type	Solid
Mounting plate description	Without mounting plate

Complementary

body type	Sides made from a single folded section Back welded with double profile forming a protected sealed area
Number of doors	Front face 1
Door opening side	Reversible 120 °)
Lock type	3 mm double-bar lock
Type of gland plate	Standard
Accessibility for operation	Front
Removable parts	Door by hinges Cable gland plate by screws
Material	Body steel
Surface finish	epoxy-polyester powder
color	Gray RAL 7035)
Standards	IEC 62208 UL CUL
Product Certifications	cUL UL DNV-GL
Product Weight	24.652 lb(US) (11.182 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environment

IP degree of protection IP66 IEC 60529

IK degree of protection IK10 IEC 62262

Ordering and shipping details

Category US10ES180034

Discount Schedule 0ES1

GTIN 3606480212079

Returnability Yes

Country of origin ES

Packing Units

Unit Type of Package 1 PCE

Nbr. of units in pkg. 1

Package 1 Height 24.02 in (61.000 cm)

Package 1 Width 8.46 in (21.500 cm)

Package 1 Length 19.88 in (50.500 cm)

Package weight(Lbs) 24.652 lb(US) (11.182 kg)

Unit Type of Package 2 PAM

Number of Units in Package 2 30

Package 2 Height 77.17 in (196.000 cm)

Package 2 Width 39.37 in (100.000 cm)

Package 2 Length 47.24 in (120.000 cm)

Package 2 Weight 767.209 lb(US) (348.000 kg)

Contractual warranty

Coverage Core product

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle)	105
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	E893f0a0-d2cc-4011-9425-3873dde70142
REACH Regulation	REACH Declaration

Use Again

Repack and remanufacture

Circularity Profile	No need of specific recycling operations
Take-back	No

Technical Illustration

Dimensions



Offer Marketing Illustration

Product benefits / Features

