

# Product data sheet

Specifications



## Climasys CC - electronic hygostat - 200-240 V - Hr 20-80% - OLED screen

NSYCCOHY230VID

**Product availability: Non-Stock - Not normally stocked in distribution facility**

### Main

Range	ClimaSys
Product name	ClimaSys CC
Product or Component Type	Electronic hygostat
Humidity setting range	20...80 %
Display Type	OLED screen
Information Displayed	Relative humidity

### Complementary

Input voltage	200...240 V AC
Maximum switching capacity	4 A 230 V AC
Electrical connection	6 terminals 2.5 mm <sup>2</sup>
Mounting Mode	By screws Clipped
Height	External: 3.3 in (85 mm)
Width	External: 2.2 in (56 mm)
Depth	External : 1.7 in (44 mm)
Mounting Location	On mounting plate Cross rails 35 mm DIN rail Spacial upright
Ambient Air Temperature for Operation	-40...176 °F (-40...80 °C)
Hysteresis	3 %
Number of outputs	2 heating function
Material	PC
Color	Light gray
Flame retardance	Self-extinguishing conforming to UL94 (material V0)
Product Certifications	UR

### Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
GTIN	3606480152634
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

---

Country of origin	CN
-------------------	----

## Packing Units

---

Unit Type of Package 1	PCE
------------------------	-----

Nbr. of units in pkg.	1
-----------------------	---

Package 1 Height	2.28 in (5.800 cm)
------------------	--------------------

Package 1 Width	2.95 in (7.500 cm)
-----------------	--------------------

Package 1 Length	3.43 in (8.700 cm)
------------------	--------------------

Package weight(Lbs)	5.432 oz (154.000 g)
---------------------	----------------------

Unit Type of Package 2	CAR
------------------------	-----

Number of Units in Package 2	75
------------------------------	----

Package 2 Height	10.63 in (27.000 cm)
------------------	----------------------

Package 2 Width	11.93 in (30.300 cm)
-----------------	----------------------

Package 2 Length	17.72 in (45.000 cm)
------------------	----------------------

Package 2 Weight	25.463 lb(US) (11.550 kg)
------------------	---------------------------

Unit Type of Package 3	PAM
------------------------	-----

Number of Units in Package 3	900
------------------------------	-----

Package 3 Height	36.61 in (93.000 cm)
------------------	----------------------

Package 3 Width	39.37 in (100.000 cm)
-----------------	-----------------------

Package 3 Length	47.24 in (120.000 cm)
------------------	-----------------------

Package 3 Weight	330.694 lb(US) (150.000 kg)
------------------	-----------------------------

## Contractual warranty

---

Coverage	Core product
----------	--------------

Warranty	18 months
----------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

Environmental Disclosure

[Product Environmental Profile](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
<a href="#">EU RoHS Directive</a>	Compliant
SCIP Number	3452f1a3-f13d-4adf-84ba-2572bcc8e35c
REACH Regulation	<a href="#">REACH Declaration</a>

## Use Again

### Repack and remanufacture

Circularity Profile	No need of specific recycling operations
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.