

Product data sheet

Specifications



Push-to-test pilot light head,
Harmony 9001SK, plastic, without
cap, 30mm, LED red, 120V

9001SKT38LR

Main

Range of product	Harmony 9001SK
Product or component type	Head for push-to-test pilot light
Light block supply	Full voltage 120 V

Complementary

Bezel material	Plastic
Mounting diameter	30 mm
Shape of signaling unit head	Round
Cap/operator or lens colour	Without cap
Light source	Red LED
Bulb base	BA 9s
Operating mode	Push-to-test
[Us] rated supply voltage	120 V
Light source colour	Red
Contacts type and composition	1 C/O
Size	30 mm
Light source	LED

Environment

Protective treatment	TC
IP degree of protection	IP66

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.080 cm
Package 1 Width	5.842 cm
Package 1 Length	11.430 cm
Package 1 Weight	113.398 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

 Repack and remanufacture	
Take-back	No