

Product data sheet

Specifications



Plug outlet, Linergy HK, 3P+Nc, 32A, 2 points, cable length 250mm

AK5PC331

Main

Range	Linergy
Product name	HK
Product or component type	Plug outlet
Poles description	3P + Nc
[I _{th}] conventional free air thermal current	10 A common mode 32 A
I ² t on activation	200000 A ² .s
Number of points	2
Number of cables	1 cable(s) 1.5 mm ² 3 cable(s) 4 mm ²
Cable length	0.25 m
Quantity per set	Set of 6

Complementary

[Ui] rated insulation voltage	600 V conforming to CSA 600 V conforming to UL 690 V conforming to IEC 60439-1
Peak current	25 kA
Electrical connection	Connector
Width	36 mm
Height	46 mm
Depth	38 mm
Product weight	0.05 kg

Environment

Standards	IEC 60439
Product certifications	CSA UL LRGS (Lloyds register of shipping) DNV

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.700 cm

Package 1 Width	12.800 cm
Package 1 Length	7.750 cm
Package 1 Weight	78.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	13.700 cm
Package 2 Width	12.800 cm
Package 2 Length	15.500 cm
Package 2 Weight	468.000 g
Unit Type of Package 3	S04
Number of Units in Package 3	96
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	8.501 kg

Contractual warranty

Warranty	18 months
----------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration

Use Again

Repack and remanufacture

Take-back	No
-----------	----