

# Product data sheet

Specifications

## Power Cord, C19 to 5-20P, 2.5m

AP9873



### Overview

Lead time Usually in Stock

### Main

Product or component type	Power cord
Input Connection Type	NEMA 5-20P
Cable length	2.5 m
Number of cables	1

### Physical

Colour	Black
Height	5.1 cm
Width	22.9 cm
Depth	10.2 cm
Product weight	0.22 kg
Mounting preference	No preference
Mounting mode	Not rack-mountable

### Input

Network frequency	50/60 Hz
permissible voltage	100...120 V
Max line current	20 A
Input current limits	20 A
Load capacity	2400 VA

### Output

Max current draw	20 A
Number of power socket outlets	1 IEC 60320 C19
Protection type	Without circuit breaker

### Conformance

Product certifications	CSA UL listed
------------------------	------------------

## Environmental

---

Ambient air temperature for operation	0...45 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	0...95 %
Storage altitude	0...15240 m

## Packing Units

---

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.2 cm
Package 1 Width	10.8 cm
Package 1 Length	31.8 cm
Package 1 Weight	0.3 kg

## Contractual warranty

---

Warranty	2 years repair or replace
----------	---------------------------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

## Environmental footprint

Environmental Disclosure

[Product Environmental Profile](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard No

Packaging without single use plastic No

[EU RoHS Directive](#) Compliant

REACH Regulation [REACH Declaration](#)

California proposition 65 WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to [www.P65Warnings.ca.gov](#)

Halogen-free status Product contains halogen above thresholds

## Use Again

### Repack and remanufacture

End of life manual availability [End of Life Information](#)

Take-back No

WEEE Label ☒ The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Image of product / Alternate images

Alternative

---

