

Product data sheet

Specifications



Current sensor relay, SE Relays,
SPDT, 15A, 24 to 240 VAC, 1 time
scale, 500 mA to 5 A, DIN mounting

841CS5-UNI

Product availability: Stock - Normally stocked in distribution
facility

Main

Product Range	Legacy
Sensory Type	Current sensor
Product or Component Type	Relay
Switch Function	SPDT
Contacts Material	AgNi
Time Delay Type	Adjustable
Rated Supply Voltage	24...240 V AC 50...60 Hz

Complementary

Time Delay Range	0...10 s
Control Type	With adjustment knob front
Nominal Output Current	15 A
Local Signalling	1 LED red 1 LED green
Repeat Accuracy	+/- 1 %
Tripping Threshold	0.5...5 A
Temperature Drift	< 0.1 %/°C
Power Consumption in VA	1.5 VA 24...240 V
Rated Operational Current	15 A at 240 V AC-1
Breaking Capacity	4000 VA AC-1
Motor Power HP	0.5 hp 120 V AC 1 hp 240 V AC
Minimum Switching Current	100 mA 5 V
Maximum Switching Voltage	250 V
Tightening Torque	7.08 lbf.in (0.8 N.m)
AWG Gauge	AWG 14
Electrical Durability	30000 cycles
Mechanical Durability	1500000 cycles
Mounting Support	35 mm DIN rail conforming to IEC 60715
Overvoltage category	III conforming to IEC 60664-1
Height	3.5 in (90 mm)
Width	0.7 in (17.6 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Depth	2.5 in (64 mm)
Product Weight	2.2 oz (63 g)

Environment

Dielectric Strength	4000 V between input and output
Standards	IEC 61010-1 EN 60255-26 EN 60255-27
Product Certifications	UL CE WEEE RoHS
Ambient Air Temperature for Storage	-22...158 °F (-30...70 °C)
Ambient Air Temperature for Operation	-4...131 °F (-20...55 °C)
IP Degree of Protection	IP20 IEC 60529 terminals) IP40 IEC 60529 front panel)

Ordering and shipping details

Category	US10CP221127
Discount Schedule	0CP2
GTIN	3606480282096
Returnability	Yes
Country of origin	CZ

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	3.54 in (9.0 cm)
Package 1 Width	0.69 in (1.76 cm)
Package 1 Length	2.56 in (6.5 cm)
Package weight(Lbs)	2.1 oz (60.0 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Height	2.95 in (7.5 cm)
Package 2 Width	3.94 in (10.0 cm)
Package 2 Length	8.74 in (22.2 cm)
Package 2 Weight	1.5 lb(US) (0.7 kg)



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov


Use Again

Repack and remanufacture

Take-back	No
-----------	----

Dimensions Drawings

Dimensions



Technical Illustration

Dimensions

