

8501XO20XLV02

NEMA Control Relay, Type X, latching, 10A resistive at 600 VAC, 2 normally open contacts, 110/120 VAC 50/60 Hz coil



Main

Range	8501X
Relay Type	Latching
Product	Relay
Current Rating	10 A AC 5 A DC
Contact Configuration	2 NO 2 standard contact cartridges
Number of Poles	2P
Coil Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Voltage Rating	600 V AC
Mounting Type	Panel
Operating Temperature	-40...160 °F (-40...71 °C)
Electrical Connection	Screw clamp terminals
Certifications	CE UL Listed CSA
Operating Time	15 ms - pick-up 13 ms - drop-out
Height	3.50 in (88.90 mm)
Width	2.23 in (56.64 mm)
Depth	6.54 in (166.12 mm)

Ordering and shipping details

Category	21158-8501 XO (AC)
Discount Schedule	CP2
GTIN	785901028499
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	21.59 in (54.839 cm)
Package 1 Width	8.50 in (21.59 cm)
Package 1 Length	54.84 in (139.29 cm)
Package 1 Weight	2.91 lb(US) (1.32 kg)
Unit Type of Package 2	PAL
Number of Units in Package 2	252
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	36.00 in (91.44 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	733.98 lb(US) (332.927 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------