

Product data sheet

Characteristics

8910DP31V14

Contactor, Definite Purpose, 30A, 1 pole, 24/24 VAC 50/60 Hz coil, open



Main

Product or Component Type	Definite Purpose Contactor
Line Rated Current	30 A
Number of Poles	1P
Pole contact composition	1 NO
Range of Product	DP

Complementary

Maximum Horse Power Rating	2 Hp 115 V AC, 1 phase 3 hp 230 V AC, 1 phase
Locked rotor rated current	125 A 460 V AC 100 A 575 V AC 150 A 277 V AC
[Ue] rated operational voltage	600 V AC
[Uc] control circuit voltage	24 V AC 50/60 Hz
Phase	1 phase
Electrical Connection	Quick connect terminals Binder head

Environment

Product Certifications	UL Recognized CSA
------------------------	----------------------

Ordering and shipping details

Category	21355-8910 DP 31
Discount Schedule	CP1B
GTIN	785901748212
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.40 in (6.096 cm)
Package 1 Width	3.40 in (8.636 cm)
Package 1 Length	2.60 in (6.604 cm)
Package 1 Weight	8.16 oz (231.332 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	12
Package 2 Height	5.90 in (14.986 cm)
Package 2 Width	7.00 in (17.78 cm)
Package 2 Length	7.30 in (18.542 cm)
Package 2 Weight	6.42 lb(US) (2.912 kg)

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------
