

# Product data sheet

## Characteristics

# 8910DP42V14

Contactor, Definite Purpose, 40A, 2 pole, 24/24 VAC 50/60 Hz coil, open



### Main

Product or Component Type	Definite Purpose Contactor
Line Rated Current	40 A
Number of Poles	2P
Pole contact composition	2 NO
Range of Product	DP

### Complementary

Maximum Horse Power Rating	2 Hp 115 V AC, 1 phase 5 hp 230 V AC, 1 phase
Locked rotor rated current	240 A 277 V AC 200 A 460 V AC 160 A 575 V AC
[Ue] rated operational voltage	600 V AC
[Uc] control circuit voltage	24 V AC 50/60 Hz
Phase	1 phase
Electrical Connection	Quick connect terminals Box lugs

### Environment

Product Certifications	UL Recognized CSA
------------------------	----------------------

### Ordering and shipping details

Category	21358-8910 DP 42
Discount Schedule	CP1B
GTIN	785901024200
Returnability	Yes
Country of origin	CN

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.30 in (5.842 cm)
Package 1 Width	2.60 in (6.604 cm)
Package 1 Length	3.40 in (8.636 cm)
Package 1 Weight	9.12 oz (258.548 g)

## Offer Sustainability

---

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

---

## Contractual warranty

---

Warranty	18 months
----------	-----------

---