

# Product data sheet

## Characteristics

# 8910DPA32V02U1

Contactor, Definite Purpose, 30A, 2 pole, 5 HP at 230 VAC, 1 phase, 110/120 VAC 50/60 Hz coil, open, UL Listed



### Main

Product or Component Type	Definite Purpose Contactor
Line Rated Current	30 A
Number of Poles	2P
Pole contact composition	2 NO
Range of Product	DPA

### Complementary

Maximum Horse Power Rating	2 Hp 115 V AC, 1 phase 5 hp 230 V AC, 1 phase
Locked rotor rated current	150 A 460 V AC 120 A 575 V AC 180 A 277 V AC
[Ue] rated operational voltage	600 V AC
[Uc] control circuit voltage	120 V AC 60 Hz 110 V AC 50 Hz
Phase	1 phase
Electrical Connection	Binder head

### Environment

Product Certifications	UL Listed CSA
------------------------	------------------

### Ordering and shipping details

Category	21343-8910 DPA 3_(30 AMP)
Discount Schedule	CP1B
GTIN	785901404347
Returnability	Yes
Country of origin	CN

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.50 in (6.35 cm)
Package 1 Width	3.20 in (8.128 cm)
Package 1 Length	4.20 in (10.668 cm)
Package 1 Weight	16.00 oz (453.592 g)

## Offer Sustainability

---

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

---

## Contractual warranty

---

Warranty	18 months
----------	-----------

---