

Product data sheet

Characteristics

8910DPA52V09

Contactor, Definite Purpose, 50A, 2 pole, 10 HP at 230 VAC, 1 phase, 208/240 VAC 60 Hz
220 VAC 50 Hz coil, open



Main

Product or Component Type	Definite Purpose Contactor
Line Rated Current	50 A
Number of Poles	2P
Pole contact composition	2 NO
Range of Product	DPA

Complementary

Maximum Horse Power Rating	3 Hp 115 V AC, 1 phase 10 hp 230 V AC, 1 phase
Locked rotor rated current	300 A 277 V AC 250 A 460 V AC 200 A 575 V AC
[Ue] rated operational voltage	600 V AC
[Uc] control circuit voltage	208...240 V AC 60 Hz 220 V AC 50 Hz
Phase	1 phase
Electrical Connection	Quick connect terminals Box lugs

Environment

Product Certifications	UL Recognized CSA
------------------------	----------------------

Ordering and shipping details

Category	21345-8910 DPA 5_(50 AMP)
Discount Schedule	CP1B
GTIN	785901080749
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.60 in (6.604 cm)
Package 1 Width	3.70 in (9.398 cm)
Package 1 Length	4.40 in (11.176 cm)
Package 1 Weight	23.04 oz (653.173 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	8
Package 2 Height	8.10 in (20.574 cm)
Package 2 Width	6.00 in (15.24 cm)

Package 2 Length	8.90 in (22.606 cm)
Package 2 Weight	11.86 lb(US) (5.38 kg)

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------

Approximate Dimensions

