

# Product data sheet

## Characteristics

# 8911DPSG23V09

Starter, Definite Purpose, nonreversing, 25A, 2 pole, 1 phase, 208 to 240 VAC coil, melting alloy overload, NEMA 1



### Main

Product	Definite Purpose Starter
Ampere Rating	25 A
Horsepower Rating	2 Hp 115 V AC, 1 phase 5 Hp 230 V AC, 1 phase 10 Hp 230 V AC, 3 phase 15 Hp 460 V AC, 3 phase 20 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Circuit Voltage	220 V AC 50 Hz 208...240 V AC 60 Hz
Phase	3 phase

### Complementary

Enclosure Material	Painted sheet steel
Enclosure Rating	NEMA 1
Locked Rotor Amperes	150 A 230 V AC 125 A 460 V AC 100 A 575 V AC
Number of Poles	3P
Range	DPS
Overload Type	Melting alloy
Number of Thermal Units	3

### Ordering and shipping details

Category	21381-8911 DP
Discount Schedule	CP1
GTIN	785901024682
Nbr. of units in pkg.	1
Package weight(Lbs)	5.87 lb(US) (2.663 kg)
Returnability	Yes
Country of origin	CN

### Packing Units

Unit Type of Package 1	PCE
Package 1 Height	6.50 in (16.51 cm)
Package 1 width	6.80 in (17.272 cm)
Package 1 Length	11.10 in (28.194 cm)

### Offer Sustainability

REACH Regulation	<input checked="" type="checkbox"/> REACH Declaration
EU RoHS Directive	Compliant <input checked="" type="checkbox"/> EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	<input checked="" type="checkbox"/> Yes
China RoHS Regulation	<input checked="" type="checkbox"/> China RoHS Declaration

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Contractual warranty

---

Warranty	18 months
----------	-----------

---