

# Product data sheet

## Characteristics

# 8911DPSG32V02

Starter, Definite Purpose, nonreversing, 30A, 2 pole, 1 phase, 110/120VAC 50/60Hz coil, melting alloy overload, NEMA 1



### Main

Product	Definite Purpose Starter
Ampere Rating	30 A
Horsepower Rating	2 Hp 115 V AC, 1 phase 5 hp 230 V AC, 1 phase
Maximum Voltage Rating	600 V AC
Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Phase	1 phase

### Complementary

Enclosure Material	Painted sheet steel
Enclosure Rating	NEMA 1
Locked Rotor Amperes	180 A 230 V AC 150 A 460 V AC 120 A 575 V AC
Number of Poles	2P
Range	DPS
Overload Type	Melting alloy
Number of Thermal Units	1

### Ordering and shipping details

Category	21381-8911 DP
Discount Schedule	CP1
GTIN	785901002826
Returnability	Yes
Country of origin	CN

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.30 in (16.002 cm)
Package 1 Width	7.00 in (17.78 cm)
Package 1 Length	11.40 in (28.956 cm)
Package 1 Weight	5.60 lb(US) (2.54 kg)

### Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>

## Contractual warranty

---

Warranty	18 months
----------	-----------

---