

# Product data sheet

## Characteristics

# 8911DPSO43V14

Starter, Definite Purpose, nonreversing, 40A, 3 pole, 3 phase, 24 VAC coil, melting alloy overload, open style



### Main

Product	Definite Purpose Starter
Ampere Rating	40 A
Horsepower Rating	3 Hp 115 V AC, 1 phase 10 Hp 230 V AC, 3 phase 7.5 Hp 230 V AC, 1 phase 20 Hp 460 V AC, 3 phase 25 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Circuit Voltage	24 V AC 50/60 Hz
Phase	3 phase

### Complementary

Enclosure Rating	Not rated (open device)
Locked Rotor Amperes	240 A 230 V AC 200 A 460 V AC 160 A 575 V AC
Number of Poles	3P
Range	DPS
Overload Type	Melting alloy
Number of Thermal Units	3

### Ordering and shipping details

Category	21381-8911 DP
Discount Schedule	CP1
GTIN	785901575009
Returnability	Yes
Country of origin	CN

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.80 in (12.192 cm)
Package 1 Width	4.80 in (12.192 cm)
Package 1 Length	7.80 in (19.812 cm)
Package 1 Weight	2.30 lb(US) (1.043 kg)

### Offer Sustainability

REACH Regulation	<input checked="" type="checkbox"/> <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <input checked="" type="checkbox"/> <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<input checked="" type="checkbox"/> <a href="#">China RoHS Declaration</a>
RoHS exemption information	<input checked="" type="checkbox"/> Yes

## Contractual warranty

---

Warranty	18 months
----------	-----------

---