

# Product data sheet

## Characteristics

# 8965DPR43V02

Reversing Hoist Contactor, 40 A, 3P, 110/120 VAC 50/60 Hz coil, open style

### Main



Product or Component Type	Reversing Hoist Contactor
Line Rated Current	40 A
Maximum Horse Power Rating	3 Hp 115 V AC, 1 phase 7.5 Hp 230 V AC, 1 phase 15 Hp 230 V AC, 3 phase 20 Hp 460 V AC, 3 phase 20 hp 575 V AC, 3 phase

### Complementary

Product Certifications	CSA UL Listed
[Ue] rated operational voltage	600 V AC
Poles description	3P
[Uc] control circuit voltage	110 V AC 50 Hz 120 V AC 60 Hz
Phase	3 phase
Range of Product	DPR

### Ordering and shipping details

Category	21403-8965DPR1>DPR4 - 20A>40A REV HOIST
Discount Schedule	CP1
GTIN	785901081357
Nbr. of units in pkg.	1
Package weight(Lbs)	2.37 lb(US) (1.075 kg)
Returnability	Yes
Country of origin	CN

### Packing Units

Unit Type of Package 1	PCE
Package 1 Height	4.70 in (11.938 cm)
Package 1 width	4.90 in (12.446 cm)
Package 1 Length	6.30 in (16.002 cm)

### Offer Sustainability

REACH Regulation	<input checked="" type="checkbox"/> <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <input checked="" type="checkbox"/> <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<input checked="" type="checkbox"/> <a href="#">Yes</a>
China RoHS Regulation	<input checked="" type="checkbox"/> <a href="#">China RoHS Declaration</a>

### Contractual warranty

Warranty	18 months
----------	-----------