



## Main

|                                 |                          |
|---------------------------------|--------------------------|
| Range of Product                | Harmony 9001SK           |
| Product or Component Type       | Head for push-button     |
| Device short name               | 9001SK                   |
| Operator profile                | Green recessed, unmarked |
| Operator additional information | Plastic guard            |

## Complementary

|                               |                       |
|-------------------------------|-----------------------|
| Mounting diameter             | 1.18 in (30 mm)       |
| Shape of signaling unit head  | Round                 |
| Type of operator              | Spring return         |
| Net Weight                    | 0.11 lb(US) (0.05 kg) |
| Bezel material                | Plastic               |
| Cap/operator or lens colour   | Green                 |
| Operator profile              | Recessed              |
| Type of operator              | Spring return         |
| Contacts type and composition | Without contact block |

## Ordering and shipping details

|                   |                   |
|-------------------|-------------------|
| Category          | 21429-9001 SK,SKY |
| Discount Schedule | CS1               |
| GTIN              | 785901042594      |
| Returnability     | No                |
| Country of origin | MX                |

## Packing Units

|                              |                    |
|------------------------------|--------------------|
| Unit Type of Package 1       | PCE                |
| Number of Units in Package 1 | 1                  |
| Package 1 Height             | 3.00 in (7.62 cm)  |
| Package 1 Width              | 2.00 in (5.08 cm)  |
| Package 1 Length             | 2.50 in (6.35 cm)  |
| Package 1 Weight             | 1.70 oz (48.081 g) |

## Offer Sustainability

|                            |                                                                                                                                                                                                                                                                                             |
|----------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                                                                                                                                                                                       |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                                                           |
| REACH free of SVHC         | Yes                                                                                                                                                                                                                                                                                         |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>                                                                                                                                                                                              |
| Toxic heavy metal free     | Yes                                                                                                                                                                                                                                                                                         |
| Mercury free               | Yes                                                                                                                                                                                                                                                                                         |
| RoHS exemption information | <a href="#">Yes</a>                                                                                                                                                                                                                                                                         |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                                                                                                                                                                                                                                                      |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                                                                                                                                                                                                               |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.                                                                                                                                                                |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|