

Product data sheet

Characteristics

9001SKRU10

30mm push button, Type SKYP, pendant station operator, two momentary push buttons, no interlock, no contacts, NEMA 4. 4X



Main

Range of Product	Harmony 9001SK
Product or Component Type	Push-button
Device short name	9001SK

Complementary

Bezel material	Plastic
Mounting diameter	1.18 in (30 mm)
Contact operation	Standard
Mechanical durability	5000000 cycles
Device presentation	Basic element

Environment

Standards	UL 508 EN/IEC 60947-5-1 JIS C 852 EN/IEC 60947-5-4 EN/IEC 60947-1 JIS C 4520 CSA C22.2 No 14
IP degree of protection	IP66
NEMA degree of protection	NEMA 1/2/3/3R/4/4X/6/12/13

Ordering and shipping details

Category	21431-9001 SKYP,SKRU
Discount Schedule	CS1
GTIN	785901526742
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.89 in (4.801 cm)
Package 1 Width	2.21 in (5.601 cm)
Package 1 Length	3.70 in (9.401 cm)
Package 1 Weight	3.84 oz (108.862 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------