

Product data sheet

Specifications



Head for pilot light, Harmony 9001K,
metal, without cap, 30mm,
380...480V

9001KP5

Main

Range of product	Harmony 9001K
Product or component type	Head for pilot light
Device short name	K

Complementary

Bezel material	Metal
Mounting diameter	30 mm
Cap/operator or lens colour	Without cap
Bulb base	BA 9s
Light block supply	Via transformer 380 V AC 50/60 Hz Via transformer 480 V AC 50/60 Hz
Shape of screw head	Round
Light source	Incandescent bulb
Operating mode	Normal
[Us] rated supply voltage	380...480 V
Light block supply	Via integral transformer
Supply frequency	50...60 Hz
Size	30 mm

Environment

Product certifications	CE CSA LR25490 class 3211 03 UL listed file E42259 CCN NKCR
NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.826 cm
Package 1 Width	5.842 cm
Package 1 Length	9.398 cm
Package 1 Weight	226.796 g



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	Ae0c4eb9-0bfb-40a4-851f-5c619fbe777d
REACH Regulation	REACH Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

Repack and remanufacture

Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins