

# Product data sheet

Specifications



Complete pre wired monolithic tower light, Harmony XVC, plastic, red orange green, 40mm, tube mounting, steady or flashing, buzzer, 100...240V AC

XVC4M35S

ⓘ To be discontinued

ⓘ To be discontinued on: May 31, 2026

## Main

Range of product	Harmony XVC4
Product or component type	Complete pre-wired monolithic tower light
Beacon or indicator bank unit type	3 illuminated units
Sound signalling	Buzzer
Mounting diameter	40 mm
Component name	XVC
Device short name	XVC
Light source	LED steady or flashing red LED steady or flashing orange LED steady or flashing green
Supply circuit type	AC
Noise level	70...85 dB (continuous or intermittent tone) at 1 m

## Complementary

Material	Polycarbonate: illuminated unit ABS (acrylonitrile butadiene-styrene): base unit PBT + ABS (UL94-V0): top cover SGP (chromium-plated): support tube
Mounting location	On support tube, 17 mm
Product mounting	On support tube, 17 mm
[Us] rated supply voltage	100...240 V
[Us] rated supply voltage	100...240 V
Cable cross section	0.33 mm <sup>2</sup> 0.83 mm <sup>2</sup>
AWG gauge	AWG 22 AWG 18
Cable length	450 mm
Marking	CE
[Uiimp] rated impulse withstand voltage	4 kV
Current consumption	80 mA
Fundamental frequency	2.23 kHz
Flashing frequency	1 Hz

Product weight	0.8 kg
Height	637.2 mm

## Environment

Standards	IEC 60947-1 IEC 60947-5-1
Product certifications	UL
Protective treatment	TC
Ambient air temperature for storage	-35...70 °C
Ambient air temperature for operation	-10...50 °C
Electrical shock protection class	Class I conforming to IEC 61140
Overvoltage category	Class I conforming to IEC 61140
IP degree of protection	IP23 vertical surface installation conforming to IEC 60529

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	74.000 cm
Package 1 Width	6.700 cm
Package 1 Length	6.700 cm
Package 1 Weight	848.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	17.000 cm
Package 2 Width	36.500 cm
Package 2 Length	76.500 cm
Package 2 Weight	9.441 kg
Unit Type of Package 3	P06
Number of Units in Package 3	20
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	27.382 kg

## Contractual warranty

Warranty	18 months
----------	-----------



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

Total lifecycle Carbon footprint

142

## Use Better

### Materials and Substances

Packaging made with recycled cardboard

Yes

Packaging without single use plastic

Yes

[EU RoHS Directive](#)

Pro-active compliance (Product out of EU RoHS legal scope)

California proposition 65

**WARNING:** This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](#)

## Use Again

### Repack and remanufacture

Take-back


No

## Dimensions Drawings

## Pre-assembled and Pre-wired Tower Light with Support Tube Mounting

## Dimensions

Below drawing shows the maximum configuration of the product. Select the number of stages according to the product characteristics in order to get **b1** dimension.




No. of illuminated units	b1 Without buzzer (mm)	b1 Without buzzer (in.)
1 stage	567.20	22.33
2 stages	602.20	23.71
3 stages	637.20	25.09
4 stages	672.20	26.46
5 stages	707.20	27.84

## Mounting and Clearance

Pre-assembled and Pre-wired Tower Light

## Support Tube Mounting



## Technical Illustration

## Dimensions

