

# ACCS1009

APC NetShelter Rack Containment, Front Assembly, for ACRC301S and ACRC301H, 300 mm



## Overview

|           |                              |
|-----------|------------------------------|
| Lead time | Usually Ships within 2 Weeks |
|-----------|------------------------------|

## Main

|                    |                    |
|--------------------|--------------------|
| Provided Equipment | Installation guide |
|--------------------|--------------------|

## Physical

|                     |                         |
|---------------------|-------------------------|
| Color               | Black                   |
| Height              | 75.24 in (191.1 cm)     |
| Width               | 11.81 in (30 cm)        |
| Depth               | 7.72 in (19.6 cm)       |
| Net Weight          | 30.07 lb(US) (13.64 kg) |
| Mounting preference | No preference           |
| Mounting Mode       | Not rack-mountable      |

## Ordering and shipping details

|                     |                         |
|---------------------|-------------------------|
| GTIN                | 731304307693            |
| Package weight(Lbs) | 49.71 lb(US) (22.55 kg) |

## Packing Units

|                  |                     |
|------------------|---------------------|
| Package 1 Height | 5.98 in (15.2 cm)   |
| Package 1 width  | 20.00 in (50.8 cm)  |
| Package 1 Length | 80.00 in (203.2 cm) |

## Offer Sustainability

|                    |                                                                                                |
|--------------------|------------------------------------------------------------------------------------------------|
| REACH Regulation   | <a href="#">REACH Declaration</a>                                                              |
| REACH free of SVHC | Yes                                                                                            |
| EU RoHS Directive  | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a> |
| Lead free          | Yes                                                                                            |

## Contractual warranty

|          |                           |
|----------|---------------------------|
| Warranty | 2 years repair or replace |
|----------|---------------------------|