



Overview

Lead time	Usually in Stock
-----------	------------------



Main

Main Input Voltage	200 V 208 V
Main Output Voltage	200 V 208 V
Plug standard	NEMA L6-30P
Number of rack unit	1U
Cable length	12 ft (3.66 m)
Provided Equipment	Installation guide Safety guide

Physical

Color	Black
Height	1.73 in (4.4 cm)
Width	17.24 in (43.8 cm)
Depth	4.96 in (12.6 cm)
Net Weight	8.38 lb(US) (3.8 kg)
Mounting Location	Front Rear
Mounting preference	No preference
Mounting Mode	Not rack-mountable
USB compatible	No

Input

Line Rated Current	24 A
Max line current	30 A
Input current limits	30 A
Load Capacity	5000 VA
Input Frequency	50/60 Hz

Output

Number of power socket outlets	4 IEC 60320 C19
--------------------------------	-----------------

Conformance

Product Certifications	CUL Listed UL Listed
------------------------	-------------------------

Ordering and shipping details

GTIN	731304327813
Package weight(Lbs)	10.14 lb(US) (4.6 kg)

Packing Units

Package 1 Height	11.06 in (28.1 cm)
Package 1 width	18.62 in (47.3 cm)
Package 1 Length	7.09 in (18 cm)
SCC14	10731304327810
Number of Units in Package 3	31

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Lead free	Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------