



Overview

Lead time	Usually in Stock
-----------	------------------



Main

Main Input Voltage	100 V 120 V 200 V 208 V 230 V 240 V
Main Output Voltage	100 V 120 V 200 V 208 V 230 V 240 V
Input Connection Type	IEC 60320 C20
Number of rack unit	1U
Provided Equipment	Installation guide Safety guide

Physical

Height	1.73 in (4.4 cm)
Width	15.28 in (38.8 cm)
Depth	3.66 in (9.3 cm)
Net Weight	3.44 lb(US) (1.56 kg)
Mounting Location	Front Rear
Mounting preference	No preference
Mounting Mode	Not rack-mountable
USB compatible	No

Input

Line Rated Current	16 A
Acceptable Input Voltage	100...240 V
Max line current	20 A
Input current limits	20 A
Load Capacity	2300 VA
Input Frequency	50/60 Hz

Output

Number of power socket outlets	7 IEC 60320 C13 2 IEC 60320 C19
--------------------------------	------------------------------------

Conformance

Product Certifications	CUL Listed CE EAC IRAM PSE UL Listed VDE
------------------------	--

Ordering and shipping details

GTIN	731304327851
Package weight(Lbs)	4.45 lb(US) (2.02 kg)

Packing Units

Package 1 Height	8.27 in (21 cm)
Package 1 width	17.17 in (43.6 cm)
Package 1 Length	2.99 in (7.6 cm)
SCC14	50731304327856
Number of Units in Package 3	100

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------