

# Product data sheet

## Characteristics

# AP8704S-NAX340

Power Cord Kit (6 ea), Locking, C13 to C14, 1.2m, North America, Red



### Overview

Lead time      Usually in Stock

## Main

Plug standard      IEC 60320 C14

## Physical

Color	Red
Height	9.45 in (24 cm)
Width	2.76 in (7 cm)
Depth	1.77 in (4.5 cm)
Net Weight	2.23 lb(US) (1.01 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

## Output

Number of power socket outlets	1 IEC 60320 C13
Cord Length	4 ft (1.22 m)

## Conformance

Product Certifications	CSA UL Listed
------------------------	------------------

## Environmental

Ambient Air Temperature for Operation	32...221 °F (0...105 °C)
Relative Humidity	20...80 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...221 °F (-25...105 °C)
Storage Relative Humidity	20...80 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

## Ordering and shipping details

GTIN	731304319689
Package weight(Lbs)	2.23 lb(US) (1.01 kg)

## Packing Units

Package 1 Height	9.45 in (24 cm)
Package 1 width	2.76 in (7 cm)
Package 1 Length	1.77 in (4.5 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Lead free	Yes
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------