



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Input Connection Type	IEC 60320 C20
Cable length	6 ft (1.83 m)
Number of cables	6

Physical

Color	Blue
Height	11.81 in (30 cm)
Width	3.15 in (8 cm)
Depth	2.76 in (7 cm)
Net Weight	4.76 lb(US) (2.16 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Max line current	16 A
Input current limits	16 A

Output

Maximum Total Current Draw per Phase	16 A
Number of power socket outlets	1 IEC 60320 C19
Cord Length	6 ft (1.83 m)

Conformance

Product Certifications	CCC CSA PSE UL Listed VDE
------------------------	---------------------------------------

Environmental

Ambient Air Temperature for Operation	32...167 °F (0...75 °C)
Relative Humidity	20...80 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...167 °F (-25...75 °C)
Storage Relative Humidity	20...80 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	731304285014
Package weight(Lbs)	4.76 lb(US) (2.16 kg)

Packing Units

Package 1 Height	11.81 in (30 cm)
Package 1 width	3.15 in (8 cm)
Package 1 Length	2.76 in (7 cm)
SCC14	10731304285011
Number of Units in Package 3	240

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------