

AP9482

StruxureWare Data Center Expert Basic Management Pack



Overview

Presentation	StruxureWare Data Center Expert Basic Management Pack provides a complete, surveillance, environmental, and physical infrastructure monitoring solution. Includes: 1 NetBotz Room Monitor 355 (with 120/240V PoE Injector), 1 NetBotz Door Switch Sensor for Rooms or 3rd Party Racks - 50 ft, 1 StruxureWare Data Center Expert Basic appliance with 25-Node License, 1 StruxureWare Data Center Expert Basic Software Support Contract
Lead time	Usually Ships within 2 Weeks

Main

Number of rack unit	1U
Number of cables	2
Communication port protocol	DHCP DNS HTTP HTTPS Modbus SMTP SMS SNMP v1 SNMP v3 SSL TCP/IP
Provided Equipment	1 Node Surveillance License Key 25-Node license key Documentation CD Installation guide

Physical

Color	Black
Height	1.73 in (4.4 cm)
Width	21.50 in (54.6 cm)
Depth	15.00 in (38.1 cm)
Net Weight	21.05 lb(US) (9.55 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Conformance

Standards	UL 60950
-----------	----------

Environmental

Ambient Air Temperature for Operation	50...95 °F (10...35 °C)
Operating altitude	0...10000 ft
Relative Humidity	5...90 %
Ambient Air Temperature for Storage	-31...140 °F (-35...60 °C)
Storage altitude	0...30000 ft (0.00...9144.00 m)
Storage Relative Humidity	5...95 %

Ordering and shipping details

GTIN	731304272496
Package weight(Lbs)	42.09 lb(US) (19.09 kg)

Packing Units

Package 1 Height	12.01 in (30.5 cm)
Package 1 width	24.76 in (62.9 cm)
Package 1 Length	30.98 in (78.7 cm)

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------