

Product data sheet

Characteristics

AP98894F

Power Cord Kit (6 ea), C19 to C20 (90 degree),
1.2m



Overview

Presentation	Low profile cord designed to eliminate space interference when accessing removable hot swap blade modules.
Lead time	Usually in Stock

Main

Plug standard	IEC 60320 C20
Provided Equipment	3 Left-angle jumper cords 3 Right-angle jumper cords

Physical

Height	24.02 in (61 cm)
Width	4.49 in (11.4 cm)
Depth	2.01 in (5.1 cm)
Net Weight	2.16 lb(US) (0.98 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Input current limits	16 A
----------------------	------

Output

Number of power socket outlets	1 IEC 60320 C19
--------------------------------	-----------------

Environmental

Ambient Air Temperature for Operation	23...140 °F (-5...60 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	11309-APC RESALE PRODUCTS
Discount Schedule	APC1
GTIN	731304261995
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	US

Packing Units

Package 1 Height	4.02 in (10.2 cm)
Package 1 width	8.50 in (21.6 cm)
Package 1 Length	5.98 in (15.2 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Lead free	Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------