

Product data sheet

Characteristics

APTF10KT01

APC 208V/120V 10KVA Step down Transformer



Overview

Lead time	Special Order - Call for Quoted Lead Times
-----------	--

General

Provided Equipment	Documentation CD Hardwire panel Installation guide Rack Mounting brackets User Manual
--------------------	---

Physical

Color	Black
Depth	29.49 in (74.9 cm)
Height	6.89 in (17.5 cm)
Product Weight	220.46 lb(US) (100 kg)
Width	17.01 in (43.2 cm)

Input

Permissible voltage	200...240 V
Max line current	60 A
Input current limits	60 A
Load Capacity	10000 VA
Input Frequency	45...65 Hz
Number of input connectors	1 Hard Wire 3-wire (2PH + G)
Nominal Input Voltage	208 V

Output

Max current draw	60 A
Number of power socket outlets	4
Protection Type	Circuit breaker
Efficiency	95 %
Number of power socket outlets	2 NEMA L5-20R 2 NEMA L14-30R
Output connector type	Hard Wire 3-wire (2PH + G) 1 Hard Wire 4-wire (2PH+N+G) 1
Output voltage	120 V 208 V 240 V

Conformance

Product Certifications	C-tick CE CSA GOST UL Listed VDE
------------------------	---

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	00731304242215
Package weight(Lbs)	275.58 lb(US) (125 kg)

Packing Units

Package 1 Height	15.98 in (40.6 cm)
Package 1 width	23.62 in (60 cm)
Package 1 Length	39.37 in (100 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACh Regulation	 REACh Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------