



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	<ul style="list-style-type: none"> Baying hardware Casters Documentation CD Door key Doors Leveling feet Rack mounting hardware Roof
--------------------	--

Physical

Maximum Mounting Depth	36.02 in (91.49 cm)
Number of rack unit	42U
Minimum Mounting Depth	10.31 in (26.19 cm)
Marking	<ul style="list-style-type: none"> 14 gauge EIA mounting rail 16 gauge front door 16 gauge post 16 gauge rear door 18 gauge roof
Color	White
Depth	42.13 in (107 cm)
Rack width	19"
Height	78.40 in (199.14 cm)
Product Weight	279.68 lb(US) (126.86 kg)
Permanent permissible load	<ul style="list-style-type: none"> 2250 Lb(US) (1020.58 kg) dynamic 3000 lb(US) (1360.78 kg) static
Width	29.53 in (75 cm)

Conformance

Standards	<ul style="list-style-type: none"> UL 2416 UL 60950-1 EIA-310E
-----------	---

Ordering and shipping details

Package weight(Lbs)	306.64 lb(US) (139.09 kg)
---------------------	---------------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Package 1 Height	87.24 in (221.6 cm)
Package 1 width	35.24 in (89.5 cm)
Package 1 Length	47.99 in (121.9 cm)
Number of Units in Package 3	1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------