

Product data sheet

Characteristics

9001SKT38LRC9

PILOT LIGHT 120V 30MM SK +OPTIONS

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Bezel material	Black plastic
Device short name	K
Enclosure type	Weatherproof enclosure dust and oil resistant indoor/outdoor Enclosure corrosion resistance indoor/outdoor
Lens type	Domed plastic
Light source	LED red
Mounting diameter	1.18 in (30 mm)

Complementary

Cap/operator or lens colour	Clear
Electrical connection	Screw clamp terminal
Light block supply	Direct
Operating mode	Push-to-test
Shape	Round head

Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/4X/6/12/13
Product certifications	CE UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03

Ordering and shipping details

Category	21429 - 9001 SK,SKY
Discount Schedule	CS1
GTIN	00785901835363
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0921 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------