

# C10BLK

## APC AV Black C Type 12 Outlet Power Filter 120V



### Overview

Lead time	Usually in Stock
-----------	------------------



### Physical

Color	Black
Cable length	10 ft (3.05 m)
Depth	2.17 in (5.5 cm)
Height	6.50 in (16.5 cm)
Net Weight	6.72 lb(US) (3.05 kg)
Width	22.72 in (57.7 cm)

### Input

Input Frequency	50/60 Hz
Switching current capacity	15 A
Nominal Input Voltage	120 V
Maximum Input Current per Phase	15 A
Plug standard	NEMA 5-15P

### Output

Number of power socket outlets	12
Outlet standard	NEMA 5-15R

### Conformance

Product Certifications	CSA
Standards	FCC Part 15 class B FCC part 68 UL 1363 UL 1449
Equipment protection policy	Lifetime : \$350000
UL 1449 TVSS Rating	330

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environmental

Ambient air temperature for operation	32...122 °F (0...50 °C)
Operating altitude	0...10000 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Storage Relative Humidity	0...95 %

## Surge Protection and Filtering

Data line protection	RJ11 Modem/Fax protection (two wire single line) RJ45 10/100/1000 Base-T Ethernet protection Cable modem/video protection Coaxial 2-Way splitter with protection
Let Through Voltage Rating	40 V
NM Surge Response Time (ns)	0 ns common mode
Common mode rejection	55 dB
Surge energy rating	3400 J

## Ordering and shipping details

GTIN	00731304236528
Package weight(Lbs)	8.49 lb(US) (3.85 kg)

## Packing Units

Package 1 Height	11.18 in (28.4 cm)
Package 1 width	30.79 in (78.2 cm)
Package 1 Length	3.23 in (8.2 cm)
SCC14	107313040
Number of Units in Package 2	4
Number of Units in Package 3	36

## Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

## Contractual warranty

Warranty	Lifetime
----------	----------