

Product data sheet

Characteristics

D10S2H

DISCONNECT SW 600VAC 60A D10 DOOR MOUNTE



Main

Range	D10S
Product	Disconnect Switch
Current Rating	60 A
Horsepower Rating	10 Hp 120 V AC 20 Hp 200/240 V AC 40 Hp 480 V AC 50 hp 600 V AC
Voltage Rating	600 V AC
Mounting Type	Door
NEMA Size	2
Service Entrance Rated	Service entrance rated

Ordering and shipping details

Category	22642 - DISCONNECT SWITCHES - D10
Discount Schedule	T
GTIN	00785901118602
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	MX

Packing Units

Package 1 Height	3.80 in (9.652 cm)
Package 1 width	8.70 in (22.098 cm)
Package 1 Length	10.20 in (25.908 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Not compliant
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------