



Overview

Lead time	Usually in Stock
-----------	------------------



Main

Cable length	5 ft (1.52 m)
--------------	---------------

General

Provided Equipment	User Manual
--------------------	-------------

Physical

Connector B	RJ45 female Cat Cat 6 Straight Through
Height	3.50 in (8.9 cm)
Connector A	RJ45 female Cat Cat 6 Straight Through
Depth	13.50 in (34.3 cm)
Net Weight	1.68 lb(US) (0.76 kg)
Width	13.50 in (34.3 cm)

Output

Number of port	6
----------------	---

Conformance

Product Certifications	TAA compliance UL Listed UL Recognized
------------------------	--

Environmental

Storage Relative Humidity	0...95 %
Storage altitude	0...10000 ft (0.00...3048.00 m)
Ambient air temperature for operation	5...113 °F (-15...45 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)

Ordering and shipping details

GTIN	00731304252269
Package weight(Lbs)	2.65 lb(US) (1.2 kg)

Packing Units

Package 1 Height	3.50 in (8.9 cm)
Package 1 width	13.50 in (34.3 cm)
Package 1 Length	13.50 in (34.3 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------