

Product data sheet

Characteristics

DDCC6-025

APC Data Distribution Cable, CAT6 UTP CMR
6XRJ-45 Black, 25FT (7.6M)



Overview

Lead time	Usually in Stock
-----------	------------------



Main

Cable length	25 ft (7.62 m)
Product Compatibility	Patch Panel

Physical

Color	Black
Height	4.49 in (11.4 cm)
Width	13.50 in (34.3 cm)
Depth	13.50 in (34.3 cm)
Net Weight	6.08 lb(US) (2.76 kg)
Mounting Mode	Not rack-mountable
Connector B	RJ45 female Cat Cat 6 Straight Through
Connector A	RJ45 female Cat Cat 6 Straight Through

Output

Number of port	6
----------------	---

Conformance

Product Certifications	TAA compliance UL Listed UL Recognized
------------------------	--

Environmental

Storage Relative Humidity	0...95 %
Storage altitude	0...10000 ft (0.00...3048.00 m)
Ambient Air Temperature for Operation	5...113 °F (-15...45 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)

Ordering and shipping details

GTIN	731304252566
Package weight(Lbs)	7.05 lb(US) (3.2 kg)

Packing Units

Package 1 Height	4.49 in (11.4 cm)
Package 1 width	13.50 in (34.3 cm)
Package 1 Length	13.50 in (34.3 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant  EU RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------