

Product data sheet

Characteristics

8910DPA62V14

CONTACTOR 600VAC 60AMP DPA +OPTIONS

Product availability: Stock - Normally stocked in distribution facility



Main

Product or component type	Definite Purpose Contactor
Line Rated Current	60 A
Number of Poles	2P
Pole contact composition	2 NO
Range of product	DPA

Complementary

Motor power hp	5 hp 115 V AC 1 phase 10 hp 230 V AC 1 phase
Locked rotor rated current	360 A 277 V AC 300 A 460 V AC 240 A 575 V AC
System Voltage	600 V AC
[Uc] control circuit voltage	24 V AC 50/60 Hz
Phase	1 phase
Electrical connection	Quick connect terminals Box lugs

Environment

Product certifications	CE CSA UL listed
------------------------	------------------------

Ordering and shipping details

Category	21346 - 8910 DPA 6_(60 AMP)
Discount Schedule	CP1B
GTIN	00785901080855
Nbr. of units in pkg.	1
Package weight(Lbs)	1.45
Returnability	Y
Country of origin	CN

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1140 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------