

# Product data sheet

## Characteristics

# HMIVXLRT4KLV80

## EcoStruxure Machine SCADA Expert 2020 for Line Manag (Runtime License), 4000 Tags



### Main

Range of Product	EcoStruxure Machine SCADA Expert
Product or Component Type	Software
User Language	Multi-language
Format	Sticker
Previous software version	V8.1 SP5

### Complementary

Range Compatibility	Harmony GTU Harmony iPC
Software Designation	Line management
Type of License	Design/operation (BT/RT)
Software Type	EcoStruxure machine SCADA Expert software
System requirements	> 2 GB HDD storage device, > 2 GB primary memory > 2 GB HDD storage device Windows 8.1, > 2 GB primary memory > 2 GB HDD storage device Windows 10, > 2 GB primary memory > 2 GB HDD storage device Windows Server 2008 R2, > 2 GB primary memory > 2 GB HDD storage device Windows Server 2012 R2, > 2 GB primary memory > 2 GB HDD storage device Windows Server 2016, > 2 GB primary memory Microsoft internet explorer 11 External audio and video files .NET Framework 3.5
Software Version	V20.0
Provided Equipment	User's documentation in electronic format
Document type	Quick start-up guide Technical reference manual Training manual
Software Function	Database connection E-signature
Audio video coding standard	MP3 WAV AVI MOV MP4 MPEG

### Ordering and shipping details

Category	22574 - MAGELIS BOX PC AND PANEL PC
Discount Schedule	MC2
GTIN	3606481171696
Nbr. of units in pkg.	1
Package weight(Lbs)	0.71 oz (20 g)
Returnability	No

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.39 in (1 cm)
Package 1 width	55.12 in (140 cm)
Package 1 Length	55.12 in (140 cm)