



Overview

Presentation	Wall mounted battery breaker box for use with open battery rack configurations.
Lead time	Usually Ships within 6 Weeks

Main

Battery Type	VRLA
--------------	------

Physical

Height	51.81 in (131.6 cm)
Width	20.31 in (51.6 cm)
Depth	7.48 in (19 cm)
Net Weight	114.00 lb(US) (51.71 kg)
Mounting Mode	Not rack-mountable

Conformance

Standards	FCC Part 15 class A UL 1778
-----------	--------------------------------

Environmental

Ambient Air Temperature for Operation	14...104 °F (-10...40 °C)
Operating altitude	0...9842 ft
Relative Humidity	0...95 % non-condensing
Ambient Air Temperature for Storage	5...104 °F (-15...40 °C)
Storage altitude	0...16404 ft (0.00...4999.94 m)
Storage Relative Humidity	0...95 % Non-condensing

Batteries & Runtime

Battery Slots Empty	0
Included Battery Modules	0
Battery Volt-Amp-Hour Capacity	0 VAh

Ordering and shipping details

GTIN	731304334729
Nbr. of units in pkg.	1
Package weight(Lbs)	188.21 lb(US) (85.371 kg)

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	72.01 in (182.9 cm)
Package 1 width	37.99 in (96.5 cm)
Package 1 Length	12.99 in (33 cm)

Contractual warranty

Warranty	1 year (parts only)
----------	---------------------