



### Overview

|              |                                                                            |
|--------------|----------------------------------------------------------------------------|
| Presentation | Battery cabinet, 39.37" wide, that includes batteries and battery breaker. |
| Lead time    | Usually Ships within 2 Weeks                                               |

### Main

|              |      |
|--------------|------|
| Battery Type | VRLA |
|--------------|------|

### Physical

|               |                          |
|---------------|--------------------------|
| Height        | 58.46 in (148.5 cm)      |
| Width         | 39.37 in (100 cm)        |
| Depth         | 33.07 in (84 cm)         |
| Net Weight    | 3359.85 lb(US) (1524 kg) |
| Mounting Mode | Not rack-mountable       |

### Environmental

|                                       |                          |
|---------------------------------------|--------------------------|
| Ambient Air Temperature for Operation | 32...104 °F (0...40 °C)  |
| Ambient Air Temperature for Storage   | 5...104 °F (-15...40 °C) |

### Batteries & Runtime

|                          |                          |
|--------------------------|--------------------------|
| Battery Slots Empty      | 0                        |
| Included Battery Modules | 0                        |
| Device mounting          | Enclosed battery cabinet |

### Ordering and shipping details

|                     |                          |
|---------------------|--------------------------|
| GTIN                | 731304343028             |
| Package weight(Lbs) | 3459.06 lb(US) (1569 kg) |

### Packing Units

|                  |                     |
|------------------|---------------------|
| Package 1 Height | 66.46 in (168.8 cm) |
| Package 1 width  | 54.02 in (137.2 cm) |
| Package 1 Length | 39.29 in (99.8 cm)  |

## Offer Sustainability

|                             |                                                                                                                                 |
|-----------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status    | Green Premium product                                                                                                           |
| REACH Regulation            | <a href="#"> REACH Declaration</a>             |
| EU RoHS Directive           | Compliant <a href="#"> EU RoHS Declaration</a> |
| Mercury free                | Yes                                                                                                                             |
| RoHS exemption information  | <a href="#"> Yes</a>                           |
| Environmental Disclosure    | <a href="#"> Product Environmental Profile</a> |
| Circularity Profile         | <a href="#"> End Of Life Information</a>       |
| Optimized Energy Efficiency | Energy efficient product                                                                                                        |
| Take-back                   | Take-back program available                                                                                                     |