

Product data sheet

Characteristics

KVM1116R

APC KVM 2G, Digital/IP, 1 Remote/1 Local User, 16 Ports with Virtual Media - FIPS 140-2



Overview

Lead time	Usually in Stock
-----------	------------------



Main

Main Input Voltage	DC 100 V 120 V 208 V 230 V 240 V
Number of rack unit	1U

Physical

Color	Black
Height	1.69 in (4.3 cm)
Width	16.69 in (42.4 cm)
Depth	7.40 in (18.8 cm)
Net Weight	5.71 lb(US) (2.59 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Input Frequency	50/60 Hz
-----------------	----------

Conformance

Product Certifications	C-tick CE EAC TAA compliance UL-AR VCCI Class A VDE
Standards	FCC Part 15 class A ICES-003 UL 60950-1

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environmental

Ambient Air Temperature for Operation	32...122 °F (0...50 °C)
Operating altitude	0...10000 ft
Relative Humidity	0...80 %
Ambient Air Temperature for Storage	-4...140 °F (-20...60 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Storage Relative Humidity	0...80 %

Ordering and shipping details

GTIN	731304340195
Package weight(Lbs)	8.80 lb(US) (3.99 kg)

Packing Units

Package 1 Height	5.75 in (14.6 cm)
Package 1 width	24.37 in (61.9 cm)
Package 1 Length	12.99 in (33 cm)

Offer Sustainability

EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes