

# KVM-DVIVMCAC

## APC KVM 2G, SERVER MODULE, DVI WITH VIRTUAL MEDIA AND CAC



### Overview

|           |                  |
|-----------|------------------|
| Lead time | Usually in Stock |
|-----------|------------------|



### Physical

|            |                       |
|------------|-----------------------|
| Color      | Black                 |
| Depth      | 4.92 in (12.5 cm)     |
| Height     | 0.55 in (1.4 cm)      |
| Net Weight | 0.29 lb(US) (0.13 kg) |
| Width      | 4.92 in (12.5 cm)     |

### Conformance

|                        |                                                |
|------------------------|------------------------------------------------|
| Product Certifications | C-tick<br>CE<br>TAA compliance<br>VCCI Class A |
| Standards              | FCC Part 15 class A<br>ICES-003<br>UL 60950-1  |

### Environmental

|                                       |                                  |
|---------------------------------------|----------------------------------|
| Ambient air temperature for operation | 32...122 °F (0...50 °C)          |
| Operating altitude                    | 0...10000 ft                     |
| Relative Humidity                     | 5...95 %                         |
| Ambient Air Temperature for Storage   | 14...140 °F (-10...60 °C)        |
| Storage altitude                      | 0...50000 ft (0.00...15240.00 m) |
| Storage Relative Humidity             | 5...95 %                         |

### Ordering and shipping details

|                     |                       |
|---------------------|-----------------------|
| GTIN                | 00731304335139        |
| Package weight(Lbs) | 0.37 lb(US) (0.17 kg) |

### Packing Units

|                  |                   |
|------------------|-------------------|
| Package 1 Height | 1.65 in (4.2 cm)  |
| Package 1 width  | 4.92 in (12.5 cm) |
| Package 1 Length | 5.08 in (12.9 cm) |
| SCC14            | 10731304335136    |

Offer Sustainability

|                            |                                                                                                                                 |
|----------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive          | Compliant  <a href="#">EU RoHS Declaration</a> |
| Mercury free               | Yes                                                                                                                             |
| RoHS exemption information |  Yes                                           |

Contractual warranty

|          |                           |
|----------|---------------------------|
| Warranty | 2 years repair or replace |
|----------|---------------------------|