

Product data sheet

Characteristics

KVM-HDMI/VMCAC

APC KVM 2G, SERVER MODULE, HDMI WITH VIRTUAL MEDIA AND CAC



Overview

Lead time	Usually in Stock
-----------	------------------



Physical

Color	Black
Height	0.55 in (1.4 cm)
Width	4.92 in (12.5 cm)
Depth	4.92 in (12.5 cm)
Net Weight	0.29 lb(US) (0.13 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Conformance

Product Certifications	C-tick CE TAA compliance VCCI Class A
Standards	FCC Part 15 class A ICES-003 UL 60950-1

Environmental

Ambient Air Temperature for Operation	32...122 °F (0...50 °C)
Operating altitude	0...10000 ft
Relative Humidity	5...95 %
Ambient Air Temperature for Storage	14...140 °F (-10...60 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Storage Relative Humidity	5...95 %

Ordering and shipping details

GTIN	731304335146
Package weight(Lbs)	0.37 lb(US) (0.17 kg)

Packing Units

Package 1 Height	1.65 in (4.2 cm)
Package 1 width	4.92 in (12.5 cm)
Package 1 Length	5.08 in (12.9 cm)
SCC14	10731304335143

Offer Sustainability

EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------