



Overview

Lead time	Special Order - Call for Quoted Lead Times
-----------	--

General

Provided equipment	Installation guide
--------------------	--------------------

Physical

Depth	21.50 in (54.6 cm)
Height	17.01 in (43.2 cm)
Net Weight	15.12 lb(US) (6.86 kg)
Width	22.01 in (55.9 cm)

Input

Max line current	300 A
Input Frequency	50 Hz 60 Hz
Nominal Input Voltage	3 phase 400 V 3 phases

Output

Maximum Total Current Draw per Phase	300 A
Output connector type	Hard Wire 3-wire (H N + E) 1
Output voltage	480 V 3 phase 400 V 3 phases

Conformance

Product certifications	CE UL Listed
------------------------	-----------------

Environmental

Ambient air temperature for operation	32...104 °F (0...40 °C)
Ambient air temperature for storage	5...104 °F (-15...40 °C)

Ordering and shipping details

GTIN	00731304267218
Package weight(Lbs)	17.42 lb(US) (7.9 kg)

Packing Units

Package 1 Height	17.01 in (43.2 cm)
Package 1 width	22.01 in (55.9 cm)
Package 1 Length	21.50 in (54.6 cm)

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------