

# Product data sheet

## Characteristics

# PD3P70AT1B

3-Pole Circuit Breaker, 70A, T1 Type for Symmetra PX250/500kW



### Overview

Lead time

Special Order - Call for Quoted Lead Times

### General

Provided equipment	Installation guide
--------------------	--------------------

### Physical

Depth	21.50 in (54.6 cm)
Height	17.01 in (43.2 cm)
Net Weight	4.01 lb(US) (1.82 kg)
Width	22.01 in (55.9 cm)

### Input

Max line current	70 A
Input Frequency	50 Hz 60 Hz
Nominal Input Voltage	3 phase 400 V 3 phases

### Output

Maximum Total Current Draw per Phase	70 A
Output connector type	Hard Wire 3-wire (3P) 1
Output voltage	480 V 3 phase 400 V 3 phases

### Conformance

Product certifications	UL Listed
------------------------	-----------

### Environmental

Ambient air temperature for operation	32...104 °F (0...40 °C)
Ambient air temperature for storage	5...104 °F (-15...40 °C)

### Ordering and shipping details

GTIN	00731304267249
Package weight(Lbs)	5.95 lb(US) (2.7 kg)

## Packing Units

Package 1 Height	170.00 in (431.8 cm)
Package 1 width	22.01 in (55.9 cm)
Package 1 Length	21.50 in (54.6 cm)

## Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

## Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------