

# Product data sheet

## Characteristics

# PDM2330L6-23-860

## APC IT Power Distribution Module 2 Pole 3 Wire 30A L2-L3 L6-30 860CM



### Overview

Presentation	Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time.
Lead time	Usually Ships within 3 Weeks

### Main

Main Input Voltage	208 V
Main Output Voltage	208 V
Provided Equipment	Installation guide

### Physical

Color	Black
Height	5.00 in (12.7 cm)
Width	17.48 in (44.4 cm)
Depth	15.98 in (40.6 cm)
Net Weight	9.46 lb(US) (4.29 kg)

### Input

Input Frequency	60 Hz
Max line current	30 A

### Output

Maximum Total Current Draw per Phase	30 A
Number of power socket outlets	1 NEMA L6-30R

### Conformance

Product Certifications	UL Listed
------------------------	-----------

### Environmental

Ambient Air Temperature for Operation	32...86 °F (0...30 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...104 °F (-15...40 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...15000 ft (0.00...4572.00 m)

### Ordering and shipping details

GTIN	731304286127
Package weight(Lbs)	11.46 lb(US) (5.2 kg)

## Packing Units

Package 1 Height	5.00 in (12.7 cm)
Package 1 width	17.48 in (44.4 cm)
Package 1 Length	15.98 in (40.6 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>
Take-back	Take-back program available

## Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------