



### Overview

|              |                                                                                                                                                                                                                  |
|--------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Presentation | Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time. |
| Lead time    | Usually Ships within 3 Weeks                                                                                                                                                                                     |

### Main

|                     |                    |
|---------------------|--------------------|
| Main Input Voltage  | 3 phase            |
| Main Output Voltage | 120 V              |
| Provided Equipment  | Installation guide |

### Physical

|            |                        |
|------------|------------------------|
| Color      | Black                  |
| Height     | 5.00 in (12.7 cm)      |
| Width      | 17.52 in (44.5 cm)     |
| Depth      | 15.98 in (40.6 cm)     |
| Net Weight | 12.24 lb(US) (5.55 kg) |

### Input

|                          |             |
|--------------------------|-------------|
| Input Frequency          | 60 Hz       |
| Acceptable Input Voltage | 200...240 V |
| Max line current         | 30 A        |

### Output

|                                      |               |
|--------------------------------------|---------------|
| Maximum Total Current Draw per Phase | 30 A          |
| Number of power socket outlets       | 1 NEMA L21-30 |

### Conformance

|                        |           |
|------------------------|-----------|
| Product Certifications | UL Listed |
|------------------------|-----------|

### Ordering and shipping details

|                     |                        |
|---------------------|------------------------|
| GTIN                | 731304272465           |
| Package weight(Lbs) | 13.43 lb(US) (6.09 kg) |

### Packing Units

|                  |                    |
|------------------|--------------------|
| Package 1 Height | 5.00 in (12.7 cm)  |
| Package 1 width  | 17.52 in (44.5 cm) |
| Package 1 Length | 15.98 in (40.6 cm) |

Offer Sustainability

|                            |                                                                                                                                 |
|----------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| REACH Regulation           | <a href="#"> REACH Declaration</a>             |
| EU RoHS Directive          | Under investigation                                                                                                             |
| Mercury free               | Yes                                                                                                                             |
| RoHS exemption information | <a href="#"> Yes</a>                           |
| Environmental Disclosure   | <a href="#"> Product Environmental Profile</a> |
| Circularity Profile        | <a href="#"> End Of Life Information</a>       |
| Take-back                  | Take-back program available                                                                                                     |

Contractual warranty

|          |                          |
|----------|--------------------------|
| Warranty | 1 year repair or replace |
|----------|--------------------------|