



Overview

Lead time	Usually Ships within 3 Weeks
-----------	------------------------------

Main

Main Input Voltage	3 phase
Main Output Voltage	208 V 3 phase
Provided Equipment	Installation guide Network Management Card

Physical

Height	78.74 in (200 cm)
Width	23.62 in (60 cm)
Depth	42.13 in (107 cm)
Net Weight	1803.78 lb(US) (818.18 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Input Frequency	60 Hz
-----------------	-------

Conformance

Product Certifications	CUL Listed UL Listed
------------------------	-------------------------

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...3333 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...30000 ft (0.00...9144.00 m)

Ordering and shipping details

GTIN	731304303381
Package weight(Lbs)	1904.00 lb(US) (863.64 kg)

Packing Units

Package 1 Height	84.65 in (215 cm)
Package 1 width	40.00 in (101.6 cm)
Package 1 Length	48.03 in (122 cm)

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------